

**G-won**

G-won Hightech Co.,Ltd.

## Digital Refract meter : GMK-701AC/702AC/703AC/704AC/705AC



Automatic Calibration & Automatic Temperature Compensation Functions are built in. Therefore, you don't need to do calibration every time when you check out the sweetness content in all kinds of foods including fruits, jams & etc. unlikely other companies' products. All you have to do is just push "Meas." button with your finger.

### Features

1. Easy to use, quick to read & compact
2. Large Digital LCD displays
3. Low battery sign appears
4. 'EM' & 'CE' marks obtained

## Specifications

Model	GMK-701AC	GMK-703AC	GMK-702AC	GMK-704AC	GMK-705AC
Measuring Ranges	0~45 Brix %	0~32 Brix %	45~90 Brix %	0~60 Brix %	25~72 Brix %
Resolution	0.1 Brix %				
Accuracy	±0.1 Brix %		±0.2 Brix %		
Power Source	Battery 9V x 1ea				
Dimensions	154(L) x 108(W) x 43(H)				
Gross Weight	Approx. 1kg				

## Measurement



1. Drip a few drops of test sample on the 'Sample Well'.
2. Place 'Light Cover' on the sample well, and press 'Meas.' button.
3. After(-) sign flickers three times, measurement result(Brix %) appears on LCD in two seconds.
4. If the test sample is out of measuring ranges, "Err" Sign appears.